





SPECIFICATION:

- MATERIAL & FINISH:SEE THE LIST;
- PLATING SPECIFICATION:
 - CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Au PLATED ON THE SOLDER AREA.
 - SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE:CLEAR ONLY
- MECHANICAL:
 - MATING FORCE:0.5~2.0kgf;
 - UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
 - DURABILITY:10000 CYCLES;
- ELECTRICAL:
 - CURRENT RATING:5A Max;
 - VOLTAGE RATING:20V Max;
 - DIELECTRIC WITHSTANDING VOLTAGE:100VAc;
 - CONTACT RESISTANCE:40mΩ Ohms Max.;
 - INSULATION RESISTANCE:100M Ohms Min.;
- ENVIRONMENTAL:
 - OPERATING TEMPERATURE:−40°C~+85°C;
 - WETTING TEMPERATURE:265±5°C,5±0.5s
 - Salt Spray Test:48H Min

NO.	PART NAME	Q'TY	MATERIAL	FINISH
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	14	Copper Alloy,T=0.15mm	Au/Sn/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0 Orange
TOLERANCE			深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.±0.50	X.*±5°	PART NO. TYPE-C-FGC057	TITLE: TYPE-C 16P直立式 DIP型 规格 H10.0mm	
X.X±0.35	X.X*±3°		MANUFACTURE DWG	
X.XX±0.25	X.XX*±2.5°			
UNITS	mm	DESIGN:	Ethan	SCALE N:A
MATERILA	— — —	CHED:	Olvia	
FINISH	— — —	APPD:	Ava	
				SHEET 1/2



说明:

- 1.每卷前后各空10PCS,尾部用美纹胶纸封住;
- 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 3.每10卷盘一叠共3000Pcs并装入1个外箱内;
- 4.在搬运过程中要轻拿轻放;
- 5.在运输中不可堆放过多(1.8M最高),不可重压;
- 6.跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跑出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY	TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
0	TYPE C RECEPTACLE		2500PCS/CARTON			PART NO. TYPE-C-FGC057	TITLE: TYPE-C 16P直立式 DIP型 规格 H10.0mm		
1	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE	X.±0.50	X.°±5°				
2	COVER TAPE	W=21.3mm	10PLATES/CARTON	X.X±0.35	X.X°±3°	DESIGN: Ethan	MANUFACTURE DWG		
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON	X.XX±0.25	X.XX°±2.5°				
4	RoHS LABEL		10PCS/CARTON	UNITS	mm	CHED: Olvia	SCALE N:A	SHEET 2/2	
5	PRODUCT LABER		10PCS/CARTON	MATERILA	---				
6	CARTON	350*340*310mm	1PCS/PACKAGE	FINISH	---	APPD: Ava			