





技术要求:

1. 表面不能有明显外观问题.
2. 先打铜底 $0.5-1\mu\text{m}$, 镀镍 $2-2.5\mu\text{m}$, 镀哑锡 $3-5\mu\text{m}$.
3. 额定电流: 60A
4. 螺纹扭矩: 13 lbf.in
5. 材质: H62



PCB.WELDING DRAWING (TOLERANCE: ± 0.05)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PCB SOLDERING TERMINAL	
DECIMALS:		PAR PCB-04-M5	
ANGLES:		DWN	
X.X ± 0.30		CHKD	
X.XX ± 0.25		APVD	
X.XXX ± 0.15		SCALE N:A	
		UNIT:MM	
		SIZE:A4	
		SHEET:1F1	
		REV:A	