





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- 技术要求:
- 1.打铜底0.5—1um,镍1.5—2.5um,镀锡2—5um.
 - 2.铆好后不得有松动现象.
 - 3.插脚尖部符合可焊性要求.
 - 4.螺纹需符合通止规/止针要求.
 - 5.M3螺纹扭矩:0.5Nm.
M4螺纹扭矩:1.0Nm.
 - 6.额定电流:35A.
 - 7.工作温度:—40℃—125℃

螺丝尺寸	型号
M3	JXT—M34001
M4	JXT—M44001



PCB.WELDING DRAWING
(TOLERANCE:±0.05)

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
.X±0.30	X.*±5°	PART NO. JXT—MN4001		TITLE: PCB SOLDERING TERMINAL		
.XX±0.25	X.X°±1°					
.XXX±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm					
MATERILA	— — —	CHED: Olvia			SCALE	SHEET
FINISH	— — —	APPD: Ava			N:A	1/1