









技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: $\leq 50\text{m}\Omega$ MAX.
6. 绝缘电阻: $\geq 500\text{M}\Omega$ Min.
7. 耐压: 150V AC/1Minute



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
JXT-FC05-LC5PH54	5	2.00	3.06	6.00	4.40	2.50	4.00
JXT-FC05-LC6PH54	6	2.50	3.56	6.50	4.90	3.00	4.50
JXT-FC05-LC7PH54	7	3.00	4.06	7.00	5.40	3.00	5.00
JXT-FC05-LC8PH54	8	3.50	4.56	7.50	5.90	4.00	5.50
JXT-FC05-LC9PH54	9	4.00	5.06	8.00	6.40	4.00	6.00
JXT-FC05-LC10PH54	10	4.50	5.56	8.50	6.90	4.00	6.50
JXT-FC05-LC11PH54	11	5.00	6.06	9.00	7.40	4.00	7.00
JXT-FC05-LC12PH54	12	5.50	6.56	9.50	7.90	4.00	7.50
JXT-FC05-LC13PH54	13	6.00	7.06	10.00	8.40	4.00	8.00
JXT-FC05-LC14PH54	14	6.50	7.56	10.50	8.90	4.00	8.50
JXT-FC05-LC15PH54	15	7.00	8.06	11.00	9.40	4.00	9.00
JXT-FC05-LC16PH54	16	7.50	8.56	11.50	9.90	4.00	9.50
.....							
JXT-FC05-LC56PH54	56	27.50	28.56	31.50	29.90	8.00	29.50
JXT-FC05-LC57PH54	57	28.00	29.06	32.00	30.40	8.00	30.00
JXT-FC05-LC58PH54	58	28.50	29.56	32.50	30.90	8.00	30.50
JXT-FC05-LC59PH54	59	29.00	30.06	33.00	31.40	8.00	31.00
JXT-FC05-LC60PH54	60	29.50	30.56	33.50	31.90	8.00	31.50

序号	品名	材质			
1	0.5掀盖立式胶芯(H=5.4)	LCP UL94V-0 本色			
2	0.5掀盖立式后盖(H=5.4)	LCP UL94V-0 黑色			
3	0.5掀盖立式端子(H=5.4)	铜合金/表面镀金			
4	0.5掀盖立式焊片(H=5.4)	铜合金/表面镀锡			
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		JXT-FC05-LCNPH54	0.5 Pitch掀盖立式正牌(H=5.4)业务图		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —				
				SCALE	SHEET
			N:A	1/1	