




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

- 技术要求:
- 1.打铜底0.5—1um, 镍2—2.5um, 镀雾锡3—5um
 2. 铆好后不得有松动现象.
 2. 插脚尖部符合可焊性要求.
 3. 螺纹需符合通止规/ 止针要求.
 4. 螺纹扭矩:0.6Nm.
 5. 额定电流:30A.



PCB.WELDING DRAWING
(TOLERANCE:±0.05)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.30	X.*±5°	PART NO.	TITLE:	
.XX±0.25	X.X°±1°	JXT-M34031	PCB SOLDERING TERMINAL	
.XXX±0.15		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia	SCALE N:A	SHEET 1/1
MATERILA	— — —	APPD: Ava		
FINISH	— — —			