













技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: $50\text{V} / \text{DC}$
4. 额定电流: $0.5\text{A} / \text{AC}$
5. 接触电阻: $\leq 0.03\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$




	REV.	ECN NO.	DESCRIPTION	DATE	DESIGN	
P/N			PIN	DIM A	DIM B	DIM C
JXT-FC05-EC5PH22			5	2.00	7.50	4.40
JXT-FC05-EC6PH22			6	2.50	8.00	4.90
JXT-FC05-EC7PH22			7	3.00	8.50	5.40
JXT-FC05-EC8PH22			8	3.50	9.00	5.90
JXT-FC05-EC9PH22			9	4.00	9.50	6.40
JXT-FC05-EC10PH22			10	4.50	10.00	6.90
JXT-FC05-EC11PH22			11	5.00	10.50	7.40
JXT-FC05-EC12PH22			12	5.50	11.00	7.90
JXT-FC05-EC13PH22			13	6.00	11.50	8.40
JXT-FC05-EC14PH22			14	6.50	12.00	8.90
JXT-FC05-EC15PH22			15	7.00	12.50	9.40
JXT-FC05-EC16PH22			16	7.50	13.00	9.90
.....						
JXT-FC05-EC47PH22			47	23.00	28.50	25.40
JXT-FC05-EC48PH22			48	23.50	29.00	25.90
JXT-FC05-EC49PH22			49	24.00	29.50	26.40
JXT-FC05-EC50PH22			50	24.50	30.00	26.90
JXT-FC05-EC51PH22			51	25.00	30.50	27.40

序号	品名	材质		
1	0.5掀盖带扣胶芯(H2.2)	LCP UL94V-0 本色		
2	0.5掀盖带扣端子(H2.2)	磷铜/表面镀锡		
3	0.5掀盖带扣后盖(H2.2)	LCP UL94V-0 黑色		
4	0.5掀盖带扣焊片(H2.2)	磷铜/表面镀锡		
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.50	±1°	PART NO.	TITLE:	
X.X±0.20		JXT-FC05-ECNPH22	Pin数 0.5 Pitch 掀盖带扣下接母(H=2.2)	
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia	SCALE SHEET	
MATERILA	— — —	APPD: Ava		
FINISH	— — —			




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V /DC
4. 额定电流: 0.5A /AC
5. 接触电阻: $\leq 0.03\Omega$ 。
6. 绝缘电阻: $\geq 100\text{M}\Omega$



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM A	DIM B	DIM C
JXT-FC05-EC52PH22	52	25.50	31.00	27.90
JXT-FC05-EC53PH22	53	26.00	31.50	28.40
JXT-FC05-EC54PH22	54	26.50	32.00	28.90
JXT-FC05-EC55PH22	55	27.00	32.50	29.40
JXT-FC05-EC56PH22	56	27.50	33.00	29.90
JXT-FC05-EC57PH22	57	28.00	33.50	30.40
JXT-FC05-EC58PH22	58	28.50	34.00	30.90
JXT-FC05-EC59PH22	59	29.00	34.50	31.40
JXT-FC05-EC60PH22	60	29.50	35.00	31.90
JXT-FC05-EC61PH22	61	30.00	35.50	32.40
JXT-FC05-EC62PH22	62	30.50	36.00	32.90
JXT-FC05-EC63PH22	63	31.00	36.50	33.40
.....				
JXT-FC05-EC92PH22	92	45.50	51.00	47.90
JXT-FC05-EC93PH22	93	46.00	51.50	48.40
JXT-FC05-EC94PH22	94	46.50	52.00	48.90
JXT-FC05-EC95PH22	95	47.00	52.50	49.40
JXT-FC05-EC96PH22	96	47.50	53.00	49.90



序号	品名	材质
1	0.5掀盖带扣胶芯(H2.2)	LCP UL94V-0 本色
2	0.5掀盖带扣端子(H2.2)	磷铜/表面镀锡
3	0.5掀盖带扣后盖(H2.2)	LCP UL94V-0 黑色
4	0.5掀盖带扣焊片(H2.2)	磷铜/表面镀锡

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.	TITLE:		
X.X±0.20		JXT-FC05-ECNPH22	*pin数 0.5 Pitch 掀盖带扣下接带扣(H=2.2)		
X.XX±0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	2/2