

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

1.MATERIAL:

HOUSING--HIGH TEMP THERMAL PLASTIC,
UL 94V-0, NATURE;

TERMINAL--COPPER ALLOY;

SHELL--COPPER ALLOY;

2.PLATING:

TERMINAL--G/F PLATING ON CONTACT AREA

G/F PLATING ON SOLDERTAIL AREA

ALL OVER 1.27 MICRON MIN.


NICKEL PLATING;

SHELL--G/F PLATING OVER ALL;

3.PATENT PRODUCT PROHIBIT COPYING:

3SMT/4SMT PCBLAYOUT

FULLY COMPATIBLE



RECOMMEND PCB LAYOUT

TOLERANCE:±0.05MM

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.38	±2°	PART NO.	TITLE:		
.XX±0.20		AIPEX-1-U,FL		RF CONN GEN I 4SMT TYPE	
.XXX±0.10		DESIGN:	Ethan	MANUFACTURE DWG	
UNITS	mm	CHED:	Olvia		
MATERILA	---	APPD:	Ava	SCALE N:A	SHEET 1/1