






NOTES:

1. MATERIAL:
CONTACT;C7701-H T=0.25±0.01mm
2. BURR NOT EXCEED 0.05mm
3. UNLESS OTHERWISE SPECIFIED ALL RADIUS ARE 0.15mm MAX
4. PLATING;PLATING NICKEL30U"~80U"
5. STORAGE;-40° C TO +85° C
6. OPERATION;-40° C TO +85° C



CROSS-HATCHED AREA DENOTES COMPONENT AND TRACE KEEP-OUT (EXCEPT CHASSIS GROUND)



PC Board Layout

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD				
CHECKED:	DATE:	TITLE: SFP笼子: SFP-1X1 焊接式笼子				
DRAWN: LYF	DATE: 2025-01-10	PART. NO.	R-SFP0W01P-L000			
		UNIT	mm	SCALE	free	
		FILE NO.	Ckmtw-SFP-0001	REV.	A	YLJM