




备注:

1. 电气性能:

- 1.1 绝缘 (Min): $100M\Omega$
- 1.2 额定电流 (Min): 1.5A
- 1.3 额定电压 (Min): 100V AC
- 1.4 端子接触阻抗 (Max): $30m\Omega$
- 1.5 工作温度: -20° -80°
- 1.7 插入力 (Max): 35N
- 1.8 拔出力 (Min): 5N
- 1.9 插拔寿命: 5000 CYCLES

2. 重点尺寸标示: "▲"


3. 所用材质需符合RoHS要求



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15
X." $\pm 2^{\circ}$ X.X" $\pm 0.5^{\circ}$



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

MICRO USB 5P 公头双面焊接90° 数据板 不包胶

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW355-USBD05-060B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2601221353

SHEET NO.

1 OF 1