









60	29.50	30.60	33.50	28.95	33.40
50	24.50	25.60	28.50	27.95	28.40
49	24.00	25.10	28.00	27.45	27.90
48	23.50	24.60	27.50	26.95	27.40
47	23.00	24.10	27.00	26.45	26.90
46	22.50	23.60	26.50	25.95	26.40
45	22.00	23.10	26.00	25.45	25.90
44	21.50	22.60	25.50	24.95	25.40
43	21.00	22.10	25.00	24.45	24.90
42	20.50	21.60	24.50	23.95	24.40
41	20.00	21.10	24.00	23.45	23.90
40	19.50	20.60	23.50	22.95	23.40
39	19.00	20.10	23.00	22.45	22.90
38	18.50	19.60	22.50	21.95	22.40
37	18.00	19.10	22.00	21.45	21.90
36	17.50	18.60	21.50	20.95	21.40
35	17.00	18.10	21.00	20.45	20.90
34	16.50	17.60	20.50	19.95	20.40
33	16.00	17.10	20.00	19.45	19.90
32	15.50	16.60	19.50	18.95	19.40
31	15.00	16.10	19.00	18.45	18.90
30	14.50	15.60	18.50	17.95	18.40
29	14.00	15.10	18.00	17.45	17.90
28	13.50	14.60	17.50	16.95	17.40
27	13.00	14.10	17.00	16.45	16.90
26	12.50	13.60	16.50	15.95	16.40
25	12.00	13.10	16.00	15.45	15.90
24	11.50	12.60	15.50	14.95	15.40
23	11.00	12.10	15.00	14.45	14.90
22	10.50	11.60	14.50	13.95	14.40
21	10.00	11.10	14.00	13.45	13.90
20	9.50	10.60	13.50	12.95	13.40
19	9.00	10.10	13.00	12.45	12.90
18	8.50	9.60	12.50	11.95	12.40
17	8.00	9.10	12.00	11.45	11.90
16	7.50	8.60	11.50	10.95	11.40
15	7.00	8.10	11.00	10.45	10.90
14	6.50	7.60	10.50	9.95	10.40
13	6.00	7.10	10.00	9.45	9.90
12	5.50	6.60	9.50	8.95	9.40
11	5.00	6.10	9.00	8.45	8.90
10	4.50	5.60	8.50	7.95	8.40
9	4.00	5.10	8.00	7.45	7.90
8	3.50	4.60	7.50	6.95	7.40
7	3.00	4.10	7.00	6.45	6.90
6	2.50	3.60	6.50	5.95	6.40
5	2.00	3.10	6.00	5.45	5.90
4	1.50	2.60	5.50	4.95	5.40
No. of Contacts	A	B	C	D	E
Dimension					

Operating Voltage (Max.): 30V AC

Current Rating (Max.): 0.2A DC

Operating Temperature: -55°C ~ +85°C

Operating Humidity range: Relative humidity 90%Max

Storage temperature range: -10°C ~ +50°C

Storage Humidity range: Relative humidity 90%Max.

1. MATERIAL:


- 1.1 HOUSING: High Temperature Plastic, UL94V-0; COLOR: NATURE.
- 1.2 ACTUATOR: High Temperature Plastic, UL94V-0; COLOR: BLACK.
- 1.3 CONTACT: Copper alloy, T=0.15±0.01mm
- 1.4 SOLDER PAD: Copper alloy, T=0.20±0.01mm

2. FINISH:

- 2.1 CONTACT: GOLD PLATING ON CONTACT AREA
GOLD PLATED ON SOLDER TAILS
NICKEL UNDER PLATED OVER ALL
- 2.2 SOLDER PAD: NICKEL PLATED OVERALL.
TIN PLATED OVERALL.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 0.5PH 2.0H 前插后压FPC	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW3D-05FPCXX-200B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2601201033
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1