









ABIDE BY ROHS



Bottom View



PCB Layout(pattern Side)



Circuit Diagram

⑫	Terminal	6	1	Brass/PBT	Plating Silver	——
⑪	Terminal	5	1	Brass/PBT	Plating Silver	——
⑩	Terminal	4	1	Brass/PBT	Plating Silver	——
⑨	Terminal	3	1	Brass/PBT	Plating Silver	——
⑧	Terminal	2	1	Brass/PBT	Plating Silver	——
⑦	Terminal	1	1	Brass/PBT	Plating Silver	——
⑥	Hookpin	——	1	Corbon Steel	——	——
⑤	Contact	——	2	Copper-Silver Composite	——	——
④	Spring	——	1	SWC	——	——
③	Base	——	1	PBT	Black	UL 94HB
②	Cover	——	1	POM	Gray	UL 94HB
①	Keystoke	——	1	POM	Black	UL 94HB
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	浙江创都电子科技有限公司			
DRAWN		2005.11.18				
CHECKED						
APPROVALS						
TOLERANCES ARE		30<L ±0.30 10<L≤30 ±0.20 5<L≤10 ±0.15 L≤5 ±0.10	ANGLE	UNIT: mm	SCALE: 2:1	PROJ:
		±2'	DRAWING NO.		SHEET	1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			