


1. 电气特性:

1-1 额定电流: 1.8A 最大

1-2 额定电压: 5V

1-3 温度范围: $-25^{\circ}\text{C} - 80^{\circ}\text{C}$

1-4 绝缘阻抗: $100\text{ M}\Omega$ MIN.

1-5 接触电阻: $40\text{ M}\Omega$ MAX

2. 机械特性:

2-1 插入力: 3.5KGF (MAX.)

2-2 拔出力: 0.5KGF (min.)

3. 寿命测试: 单面3000次循环

4. 表示"▲"重点尺寸



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: MICRO USB 5P 公头双面焊接90° 数据板包胶	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW353-USBD05-167B	MOLD NO.
UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2601221339	SHEET NO. 1 OF 1