








REV.	ECN NO	LOCATIONS	DESCRIPTION	DATE



Specifications:

1. Electrical:

- 1.1 Current Rating:1.8A/contact terminal
- 1.2 Voltage Rating:30V DC
- 1.3 Contact Resistance:50 milliohms Max
- 1.4 Dielectnic Withstanding Voltage:
300 V AC AT Sea Level
- 1.5 Insulation resistance:100MEGA ohms MIN

2. Mechanical:

- 2.1 Cnector Mate and Unmate Force
Mate force:3.0kgf (Max)
Unmate force:0.7kgf (MIN)
- 2.2 Durability:2000 cycles

3. Matorial:

- 3.1 Housing:
Hing Temperature Tnermaplastics,
U1 94V-0 LCP Black
- 3.2 Contact C5191-EH
- 3.3 Shell: H65 EH0.3MM

4. PLATING:

- 4.1 Contact: Plated Gold in Mating Area;
Tin On Solder Tails
- 4.2 Shell:Nickel 50u"Min Plated.

PART NO: A01SBXXXXXX1-067		MATERIAL		浙江创都电子科技有限公司		
MODEL NO: XX		FINSH:				
UNIT: MM	SIZE: A4	COLOR:		TITLE: MicroXNJ-P-SJ-WCJ MIRCO USB 5S B TYPE 四脚全插(牛角型)短针		
TOLERANCE UNSPECIFIED .x 0.25 .xx 0.15 .xxx 0.10 Ang. 2°		DR:				
		CHK:		DWG NO: A067	REV: A	
		APP:		SCALE: 5:1	DATE: 2012.05.02	