





RoHS Component

“*” Pivot Dimension



PCB LAYOUT

P0(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
009	16.92	24.99	30.81	19.28
015	25.25	33.32	39.14	27.51
025	38.96	47.04	53.04	41.28
037	55.42	63.50	69.32	57.71

NOTICE :

1. ELECTRIC:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 5AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.at 500V DC

DIELECTRIC STRENGTH: 500V AC RMS for 1Minute

OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G. F(UL94V-0), BLACK COLOR.

CONTACT: COPPER ALLOY

CONTACT PLATED:GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELLPLATED:NICKEL/TIN

FORK/NUT:COPPER ALLOY/PLATED NICKEL

浙江创都电子科技有限公司


TOLERANCE:

XX ±0.38

XX ±0.25

XXX ±0.13

X° ±5° XX° ±2°



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

DATE :

2009. 08. 22

PART NAME:

DP XP 公 直焊板式铆鱼叉锁丝

CHECKED BY:

DATE :

2009. 08. 22

DRAW NO.

DP-G-*P-YCLS-GK-180

APPROVED BY:

DATE :

2009. 08. 22

PART NO.

REMARK

MOLD NO.