







ABIDE BY ROHS



PCB Layout Recommended



|      |           |         |      |                         |           |        |
|------|-----------|---------|------|-------------------------|-----------|--------|
| ⑨    | Keystoke  |         | 1    | POM                     | Blue      | UL94HB |
| ⑧    | Contact   |         | 2    | Copper-silver Composite | Ag-Plated |        |
| ⑦    | Cover     |         | 1    | POM                     | White     | UL94HB |
| ⑥    | Hookpin   |         | 1    | Steel                   |           |        |
| ⑤    | Spring    |         | 1    | SWC                     |           |        |
| ④    | Base      |         | 1    | PBT                     | Black     | UL94HB |
| ③    | Terminal  | 3       | 1    | Brass                   | Ag-Plated |        |
| ②    | Terminal  | 2       | 1    | Brass                   | Ag-Plated |        |
| ①    | Terminal  | 1       | 1    | Brass                   | Ag-Plated |        |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL                | FINISHING | REMARK |

|                |  |         |              |                   |              |                                                                                             |
|----------------|--|---------|--------------|-------------------|--------------|---------------------------------------------------------------------------------------------|
| APPROVALS      |  | DATE    | 浙江创都电子科技有限公司 |                   |              |                                                                                             |
| DRAWN          |  | L       | 08.09.09     | KFC-22Z88-GT-PBTK |              |                                                                                             |
| CHECKED        |  |         |              | TITLE:            | 8.0自锁6p蓝白黑   |                                                                                             |
| APPROVALS      |  |         |              | PART NO.          |              |                                                                                             |
| TOLERANCES ARE |  | 30<L    | ±0.30        | ANGLE             | UNIT: mm     | SCALE: 5:2                                                                                  |
|                |  | 10<L≤30 | ±0.20        |                   |              |                                                                                             |
|                |  | 5<L≤10  | ±0.15        |                   |              |                                                                                             |
|                |  | L≤5     | ±0.10        | ±2'               | DRAWING NO.  | PROJ:  |
|                |  |         |              |                   | SHEET 1 OF 1 |                                                                                             |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|         | A    |       | NEW          |         |        |        |