




NOTE:  
 MATERIAL:  
 1. TERMINAL: COPPER ALLOY  
 2. HOUSING: LCP UL 94V-0. COLOR: BLACK

MECHANICAL REQUIREMENT:  
 1. DURABILITY: 100 CYCLES MIN.  
 2. INSERTION AND EXTRACTION FORCE: 40N MAX & 11.5N M-ENVIRONMENTAL:  
 1. CONTACT RESISTANCE: 20 MILLIOHMS MAX INITIAL.  
 2. DIELECTRIC WITHSTANDING VOLTAGE: 300V AC/MIN.  
 3. OPERATION: -40°C~+85°C.  
 4. STORAGE: -55°C~+105°C.  
 5. REFLOW SOLDERING TEMPERATURE: 255~265° MAXIMUM FOR 5~10 SECONDS.  
 6. ROHS COMPLIANT



RECOMMENDED PCB LAYOUT(TOP VIEW)  
 (ALL TOLERANCES ARE ±0.05)

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD				
CHECKED:	DATE:	TITLE: SFP座子: SFP-20PIN 内芯 贴面带柱				
DRAWN: LYF	DATE: 2025-01-10	PART. NO.	R-SFPOM01P-D000			
		UNIT	mm	SCALE	free	
		FILE NO.	Ckmtw-SFP-0003	REV.	A	YLJM