








ABIDE BY WEEE & ROHS



MOUNTING SURFACE



PCB Layout Recommended

⑨	Keystoke		1	POM	Blue	UL94HB
⑧	Contact		2	Copper-silver Composite	Ag-Plated	
⑦	Cover		1	POM	White	UL94HB
⑥	Hookpin		1	Steel		
⑤	Spring		1	SWC		320±50gf
④	Base		1	PBT	Black	UL94V-0
③	Terminal	3	1	Brass	Ag-Plated	
②	Terminal	2	1	Brass	Ag-Plated	
①	Terminal	1	1	Brass	Ag-Plated	
ITEM	PART NAME	TER'NO.	QTY.			REMARK

APPROVALS		DATE	浙江创都电子科技有限公司	
DRAWN	LEIJUAN	08.09.09		

CHECKED				8.0无锁无声蓝白黑
APPROVALS				KFC-22W88-GT-PBTK
TOLERANCES ARE	30<L 10<L<30 5<L<10 L<5	±0.30 ±0.20 ±0.15 ±0.10	ANGLE ±2°	PROJ:

ECN NO.	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A						