




## 备注:

1. 材质: 胶芯LCP, 舌片LCP

端子: C5210,  $t=0.15\text{mm}$ 外壳: SUS301,  $t=0.20\text{mm}$ 

## 2. 电气性能:

2.1 绝缘 (Min):  $100\text{M}\Omega$ 2.2 额定电流 (Min):  $1.5\text{A}$ 2.3 额定电压 (Min):  $100\text{V AC}$ 2.4 端子接触阻抗 (Max):  $30\text{m}\Omega$ 2.5 工作温度:  $-20^{\circ} - 80^{\circ}$ 2.7 插入力 (Max):  $35\text{N}$ 2.8 拔出力 (Min):  $5\text{N}$ 

2.9 插拔寿命: 5000 CYCLES


## 3. 重点尺寸标示: "▲"

4. 所用材质需符合RoHS要求



深圳市华宇创精密电子有限公司

## TOLERANCE:

X.X  $\pm 0.30$ X.XX  $\pm 0.25$ X.XXX  $\pm 0.15$ X."  $\pm 2^{\circ}$  X.X"  $\pm 0.5^{\circ}$ 

UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

MICRO USB 5P 公头双面四五不短路 不包胶

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW354-USBD05-148B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2601221346

SHEET NO.

1 OF 1