








ABIDE BY ROHS




BOTTOM VIEW



BOTTOM VIEW



Circuit Diagram



PCB Layout Recommended

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑦	Hookpin		1	Carbon Steel		
⑥	Contact		1	Copper-Silver Composite		
⑤	Terminal		6	Brass /PBT	Plating Silver	
④	Spring		1	SWC		
③	Base		1	PBT	Black	
②	Cover		1	POM	Gray	
①	Keystoke		1	POM	White	

APPROVALS DATE

DRAWN 2006.11.26

CHECKED

APPROVALS

TOLERANCES ARE

 $30 \leq L \leq 30 \pm 0.30$  mm

 $10 \leq L \leq 30 \pm 0.20$  mm

 $5 \leq L \leq 10 \pm 0.15$  mm

 $L \leq 5 \pm 0.10$  mm
ANGLE  $\pm 2^\circ$ 

UNIT: mm

SCALE: 2:1

PROJ:

DRAWING NO.

SHEET 1 OF 1

浙江创都电子科技有限公司

ECN NO.	REV.	DATE.	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	APPROVALS	DATE	TITLE:	PART NO.
	A									8.5 无锁 -	KFC-22W85-GTPN-PBTK