








ABIDE BY WEEE & ROHS



Circuit Diagram



PCB Layout (Pattern Side)

⑦	Terminal		5	Brass	Plating silver	
⑥	Hookpin		1	Stainless Steel		
⑤	Contact		1	Copper Silver	Plating silver	
④	Spring		1	Stainless Steel		
③	Base		1	PA66	Gray	UL94V-0
②	COVER		1	POM	Black	
①	keystoke			POM	Gray	
ITEM	PART NAME	TER'NO.	QTY	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		浙江创都电子科技有限公司			
DRAWN		2008.09.03					
CHECKED				TITLE:	5.8无锁6P灰导		
APPROVALS				PART NO.	KFC-22W58-GT-PPAK		
TOLERANCES ARE		30~100	±0.30	ANGLE	UNIT: mm	SCALE: 2:1	
		10~30	±0.20				PROJ:
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.			
						SHEET 1 OF 1	