



○形大脚

- NOTES:
1. MATERIAL;
CONTACT;C7701-H T=0.25±0.01mm
 2. BURR NOT EXCEED 0.05mm
 3. UNLESS OTHERWISE SPECIFIED ALL RADIUSES ARE 0.15mm MAX
 4. PLATING;PLATING NICKEL30U~80U
 5. STORAGE;-40° C TO +85° C
 6. OPERATION;-40° C TO +85° C



CROSS-HATCHED AREA DENOTES COMPONENT AND TRACE KEEP-OUT (EXCEPT CHASSIS GROUND)



PC Board Layout
PC Board Layout

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: SFP笼子: SFP-1X1-压接式笼子			
DRAWN: LYF	DATE: 2025-01-10	PART. NO.	R-SFP0K01P-L000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-SFP-0002	REV.	A