









RoHS
Compliant



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X. ± 0.50	X.° ± 2°	UNITS mm
.X ± 0.30	.X° ± 1°	
.XX ± 0.10	.XX° ± 0.5°	MAT'L
.XXX ± 0.05		
		FINISH
		Q'TY

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



特性: RECOMMENDED P.C.B. LAYOUT (俯视图)
TOLERANCE UNSPECIFIED ±0.05mm

一、电气性能: ELECTRICAL

- 额定电流: 5.0A
- 接触阻抗: 40 MILLIOHMS MAX
- 耐电压: 150V AC / 1 mA MAX
- 绝缘阻抗: 150V DC/100 MEGA OHMS MIN

二、机械性能:

- 插入力: 5~20N
- 拨出力: 8~20N
- 使用寿命: 10000次、拨出力 6N MIN

三、材料: MATERIAL

- 塑胶: LCP/PA9T UL94V-0
- 端子: C7025 T=0.15MM
- 外壳: SUS304 T=0.30MM
- 卡勾: SUS304 T=0.15MM

四、电镀: FINISH

- 端子: 接触点镀金1U"MIN
PIN脚焊接区域镀金1U"MIN.
- 外壳: 镀镍50U"MIN (盐雾48H)


五、电镀品需做粘锡测试: 粘锡面积达到95%以上。

六、SMT回流焊 (峰值260° C±5° C) 不能气泡、
熔胶、变色不良 (变形在公差范围以内)

七、工作温度: -40° C~+85° C

浙江创都电子科技有限公司

TITLE:
TYPE-C-16PLC-H**-A



SCALE	SHEET	REV.
1/1	1/1	A1