

NOTES:

1. CURRENT RATING:
3.0A MAX.
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
-30 °C ~ 85 °C.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.
- 10: MARK "▼" AS THE FOCUS,
FIRST ITEM INSPECTION.
- 11: MARK "⊗" TO MEASURE DIMENSIONS
FOR FAI.

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SUB1	VBUS	RX2-	RX2+	GND
GND	RX1+	RX1-	VBUS	SUB2	D-	D+	CC2	VBUS	TX1-	TX1+	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TABLE:


INSERT MOLD	SHELL	Stainless Steel,T=0.15mm;	Ni:50u"Min
	LATCH	Stainless Steel,T=0.3mm;	Electroplated semi-nickel matte tin;50u"Min;
	EMC SPRING	Stainless Steel,T=0.10mm	-----
	CONTACT	Copper Alloy,T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1u", Solder AREA:Sn 50-100u"
	PLASTIC	LCP(G.F30%) BLACK.	-----
P/N	PART NAME	MATERIALS	FINISH



深圳市华宇创精密电子有限公司

TOLERANCE:

x.x ±0.30
x.xx ±0.25
x.xxx ±0.15
x.' ±2" x.x' ±0.5"



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

CHECKED BY:

马跃

DATE :

2014-02-23

APPROVED BY:

邱敏

DATE :

2014-02-23

PART NAME:

USB TYPE C 公座24P 立贴11.0H 无DIP脚

PART NO.

HYCW668-USBC24-110B







MOLD NO.

DRAW NO:


HYC-2601061627

SHEET NO.

1 OF 1



截面 A-A



RECOMMENDED PCB LAYOUT
PCB THICKNESS 0.7mm
GENERAL TOLERANCE ±0.05