





RoHS Component

“*” Pivot Dimension



PCB LAYOUT

品名规格

*	DP 9P 母 铆鱼叉锁丝 H=6.0	PDP009FH06000014801000	12800058
*	DP 25P 母 铆鱼叉锁丝 H=6.0	PDP025FH06000014801000	12800062

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
009	16.33	24.99	30.81	19.28
015	24.66	33.32	39.14	27.51
025	38.38	47.04	53.04	41.28
037	54.84	63.50	69.32	57.71

NOTICE :

1. ELECTRIC:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 5AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.at 500V DC

DIELECTRIC STRENGTH: 500V AC RMS for 1Minute

OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G. F(UL94V-0), BLACK COLOR.

CONTACT: COPPER ALLOY

CONTACT PLATED:GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELLPLATED:NICKEL/TIN

FORK/NUT:COPPER ALLOY/PLATED NICKEL

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X° ±5° XX° ±2°		DRAWN BY :	DATE : 2009. 08. 22	PART NAME: DP XP 母 直焊板式铆鱼叉锁丝	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4			CHECKED BY:	DATE : 2009. 08. 22	DRAW NO. DP-M-9P-YCLS-GK-180
		APPROVED BY:	DATE : 2009. 08. 22	PART NO.	
				REMARK 2	
				MOLD NO.	