







ROHS



Circuit Diagram



PCB Layout Recommended

ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
7	Hookpin			1	Carbon Steel	
6	Contact			2	Copper-Silver Composite	
5	Terminal			6	Brass	Plating silver
4	Spring			1	Stainless Steel	
3	Base			1	PPA	Gray
2	Cover			1	POM	Black
1	Keystoke			1	POM	White

APPROVALS		DATE	浙江创都电子科技有限公司			
DRAWN		2005.10.29				
CHECKED		2005.10.29	TITLE:	5.8自锁按键开关		
APPROVALS		2005.10.29	PART NO.	KFC-22Z58-GT-PPAK		
TOLERANCES ARE		$30 \leq L \leq 30$ $\pm 0.30$ $10 \leq L \leq 30$ $\pm 0.20$ $5 \leq L \leq 10$ $\pm 0.15$ $L \leq 5$ $\pm 0.10$	ANGLE $\pm 2^\circ$	UNIT: mm $\pm 2^\circ$	SCALE: 3:1	PROJ.:
				DRAWING NO.		SHEET 1 OF 1