




**RoHS
Compliant**





NO	CONTENTS OF CHANGE	RVS	APV	M/D/Y
1		R01		
1		R02		





- 规格说明: Specifications:
电气特性: Electrical:
- 额定电流: Current Rating
1.0A/contact termin
 - 额定电压: Voltage Rating
30V DC
 - 接触电阻: Contact Resistance
30 milliohms MAX
 - 耐压: Dielectric Withstanding Voltage
300 V AC AT Sea Level
 - 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

- 物理性能: Mechanical:
- 插拔力: Connector Mate and Unmate Force
Mate force: 1.0 kgf (MAX)
Unmate force: 0.7kgf (MIN)
 - 端子保持力: Terminal Retention
0.3kgf (MIN)

- 原材料: Material:
- 壳体: Housing:
Hing Temperature Thermoplastics,
Ul PBT White/Black
 - 端子: Contact: Copper Alloy
 - 壳体: Shell: Copper Alloy SPCC/C268
- 电镀: Finish:
- 端子: Contact: Plated Gold in Matte
Tin On Solder Tails
 - 壳体: Shell:
Nickel Plating



RECOMMENDED
P.C.B
HOLE
LAYOUT
TOP
VIEW (TOLERANCE: ±0.05)



TERMINAL ASSIGNMENT

CONTACT NUMBER	CONDUCTOR
1	V+5V
2	D-
3	D+
4	GND

TERMINAL ASSIGNMENT

CONTACT NUMBER	CONDUCTOR
5	SHIELD
6	SHIELD
7	GND
8	SHIELD
9	SHIELD

Part Name	MATERIAL	THICK	FINISH	Q'TY	产品料号
5 SHELL-B	SUS201	1-0.30	Ni:40u"Min	1	PS200A109
4 SHELL-A	SPCC	1-0.35	Ni:40u"Min	4	PS200A109
3 TERMINAL-A	BRASS	1-0.2	Sn60U+Au0.5U	18	
2 Subject	PBT	/	Blue	1	
1 HOUSING	PBT	/	Blue	1	

连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

项目名称		数量		料厚	0.30	产品料号	TCB451
单位	MM			材质	SPCC/C2680	图号	
X	±0.5mm	X°	±1°	表面处理	见备注	产品名称	
XX	±0.25mm	XX°	±1°	USB 3.0 A F 90度18P双层有后盖有边DIP			
XXX	±0.15mm	XXX°	±0.5°				
	±0.05mm		±0.5°				