

RoHS
Compliant



结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
0	原始图档		JACK	Yang	190606





备注:

1. 材料: LCP黑色, 黄铜镀金;
1. 额定电压: AC/DC 30V Max
2. 绝缘耐压: AC 1000V 1 MINUTE, 无损伤
3. 绝缘电阻: DC 500V 1 MINUTE, 1000M Ω Min
4. 操作温度: -20° to +80°
5. 料号说明: JMETM06-K XX

03:3PIN
04:4PIN
.....



Recommended P.C.Board Layout



PIN	Dim. A	Dim. B	Dim. C	Dim. D
02pin	5.85	4.45	4.00	2.00
03pin	7.85	6.45	2.00	4.00
04pin	9.85	8.45	4.00	6.00
05pin	11.85	10.45	6.00	8.00
06pin	13.85	12.45	8.00	10.00
07pin	15.85	14.45	10.00	12.00
08pin	17.85	16.45	12.00	14.00

QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司		
▽₀ ▽_C		MM		INCH	MATERIAL:	HRC:	TITLE: MINI 2.0PH H=2.0mm 卧贴式			
	.X	±0.25	.X	②	DRAWN BY JK-YANG DATE					
	.XX	±0.15	.XX	③			CHECKED BY DATE			
	.XXX	±0.05	.XXX	④	THIRD ANGLE PROJECTION					
	ANGULAR ±1°					APPROVED BY DATE		PART NO. JMETM06-K XX-B-B		REVISE ON CAD ONLY
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										