









Poles	PART NO.	Dimension mm		
		A	B	C
2	W-NH10M02P-B000	1.00	3.60	2.40
3	W-NH10M03P-B000	2.00	4.60	3.40
4	W-NH10M04P-B000	3.00	5.60	4.40
5	W-NH10M05P-B000	4.00	6.60	5.40
6	W-NH10M06P-B000	5.00	7.60	6.40
7	W-NH10M07P-B000	6.00	8.60	7.40
8	W-NH10M08P-B000	7.00	9.60	8.40
9	W-NH10M09P-B000	8.00	10.60	9.40
10	W-NH10M10P-B000	9.00	11.60	10.40
11	W-NH10M11P-B000	10.00	12.60	11.40
12	W-NH10M12P-B000	11.00	13.60	12.40
13	W-NH10M13P-B000	12.00	14.60	13.40
14	W-NH10M14P-B000	13.00	15.60	14.40
15	W-NH10M15P-B000	14.00	16.60	15.40

NOTES:

- Material:
Insulation:Thermal Plastic, UL94V-0(Nature)
Pin:Phosphor Bronze/Tin-Plated
Tab:Phosphor Bronze/Tin-Plated
- Current Rating: 1A AC,DC
- Voltage Rating: 125V AC,DC
- Temperature Rang: -25°C~+85°C
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 100MΩ Min
- Withstanding Voltage: 500V AC/minute

P.C.B Layout

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: NH1.0SMT-XP 带扣 卧贴					
DRAWN: LYF	DATE: 2025-05-07	PART. NO.		W-NH10MXXP-B000			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-NH1.0-B003		REV.	A	XR00