


Features:

- 1. 2~12 circuits available;
- 2. Material: PA66+15%GF, Black color;
- 3. Contact: Brass;
- 4. Finished: Tin-plated;
- 5. 0.64mm square pin;
- 6. Mates with H3000S12-XX housing;



Specification:

- Current rating: 5A AC/DC
- Voltage rating: 250V AC(RMS) or 250V DC Max
- Contact resistance: 10mΩ Max
- Insulation resistance: 1000MΩ Min
- Dielectric withstanding voltage: 1500V AC/minute
- Ambient temperature rang: -20°C~+85°C


Dimensional Information(mm)

Circuits	DIM A	DIM B	Circuits	DIM A	DIM B
02	3.00	9.65	08	21.00	27.65
03	6.00	12.65	09	24.00	30.65
04	9.00	15.65	10	27.00	33.65
05	12.00	18.65	11	30.00	36.65
06	15.00	21.65	12	33.00	39.65
07	18.00	24.65			


H3000S13-XX

SERIES NO: _____




PIN Q'PY: _____
02~12




Circuit 1




P C B LAYOUT




2 CKTS




03 CKTS




05 CKTS




10 CKTS




09 CKTS




04 CKTS




08 CKTS




07 CKTS



06 CKTS



11 CKTS



12 CKTS

REV	Description	DATE	GENERAL TOLERANCES (unless specified)	UNITS	MM	DATE	2014-03-05
			X.X±0.4	SCALE	1:1	DRAWING	Liu zhi guo
			X.XX±0.25	REV	A	CHECKED BY	Li peng
			X.XXX±0.15	APPROVAL BY	OYSW		

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

PRODUCT NAME: 3.0 mm vertical header
PART NUMBER: H3000S13-XX