





??	????	??	???	??
Mapx	Modification	Date	Draw	Approve
▲				



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

1. 塑胶: Housing:
Hing Temperature Thermoplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Talls
端子四周镀50U”(MIN)锡, 镀金区域镀100-200U”镀金1U”
2. 外壳: Shell:
铜壳四周镀80U”(MIN)锡
Nickel Plating

成品图 MANUFACTURE DWG		LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD							
公差一览表 TOLERANCE UNLESS OTHERWISE		??	??	??	??	??	??	??	??
.X±0.15	.X±5'	DATE	DATE	UNIT	MM	DRAWING	DRAWN	DWG NO.	DWGNO. TCB644
XX±0.05	.X±2'	CHECKED	CHECKED	SCALE	1:1	DESIGN	LIUFU	品名	沉板外壳
XXX±0.02	.XX±1'	APPROVE	APPROVE	VIEW	⊕			版本	VER
								页教	PG1

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作