






REV	LTR	DESCRIPTION	DATE	APPROVED



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf (MAX)  
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention  
1.2kgf (MIN)

原材料: Material:

1. 塑胶: Housing:  
PBT WHITE/BLACK
2. 外壳: Shell: SPCC  
Nickel Plating
2. 端子: Contact: Copper Alloy C2680

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Tails

TOLERANCES	
. X	±0.30
. XX	±0.20
. XXX	±0.10
ANGLES	±2.00°

**LXW** 连兴旺电子(深圳)有限公司  
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

APPROVED:	TITLE: 0 USB AF 双层90°弯脚 卷边			
CHECKED:	PART NO.: TCB146	PROJECTION:		
DRAWING:	REV.: A/0	SIZE: A4	UNIT: M M	SCALE: 1:1 SHEET: 1/1