

电气特性/Electrical Specification



额定参数/Rated	300V 8A
接触电阻/Contact Resistance	20mΩ MAX
绝缘电阻/Insulation Resistance	5000mΩ/1000V
抗电强度/Dielectric Strength	2000V/1 min

机械特性/Mechanical Specification

使用温度/Temp range	-40° C ~ +105° C
瞬间温度/MAX Soldering	+250° C/5s

部件材质/Part&Material

塑件/Housing	PA66 UL94 V-0
端子/Terminal	黄铜 镀锡/Brass Tin plating



间距公差/Spacing tolerance(mm)					—			 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD							PART NAME:		
X.	X.X	X.X.X	0.1/10		PART NO:LXW15EDGVC-3.81-NP												
±0.5	±0.30	±0.1	∠ ±2°		DRAWING NO:												
未注公差/General tolerances(mm)					STATUS	APPD	CHKD	DRFT	DATE	CUSTOM	PROJECT	UNITS	TYPE: CUSTOMER DRAWINGS				
0---30	31---50	51---80	81---120	>121									REV	SIZE	SHEET		
±0.30	±0.50	±0.70	±1.05	±1.20									A	A4	1/1		