

Features:

- 1. 2~12 circuits available;
- 2. Material: Pa66+15%GF UL94V-0, Black color;
- 3. Contact: Brass;
- 4. Finished: Tin-plated;
- 5. 0.64mm square pin;
- 6. Mates with H3000S12-XX housing;








Specification:

Current rating: 5A AC/DC
 Voltage rating: 250V AC(RMS) or 250V DC Max
 Contact resistance: 10mΩ Max
 Insulation resistance: 1000MΩ Min
 Dielectric withstanding voltage: 1500V AC/minute
 Ambient temperature rang: -20°C~+85°C

Dimensional Information(mm)

Circuits	DIM A	DIM B	Circuits	DIM A	DIM B
02	3.00	9.65	08	21.00	27.65
03	6.00	12.65	09	24.00	30.65
04	9.00	15.65	10	27.00	33.65
05	12.00	18.65	11	30.00	36.65
06	15.00	21.65	12	33.00	39.65
07	18.00	24.65			

H3000S14-XX
 SERIES NO: _____
 PIN Q'PY: _____
 02~12




REV	Description	DATE	GENERAL TOLERANCES (unless specified)	UNITS	MM	DATE	2014-03-05
			X.X±0.4	SCALE	1:1	DRAWING	Liu zhi guo
			X.XX±0.25	REV	A	CHECKED BY	Li peng
			X.XXX±0.15	APPROVAL BY		OYSW	




连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD


PRODUCT NAME	3.0 mm right angle header
PART NUMBER	H3000S14-XX




12 CKTS




04 CKTS




09 CKTS




2 CKTS




11 CKTS




05 CKTS




08 CKTS




03 CKTS



10 CKTS



06 CKTS



07 CKTS

REV	Description	DATE	GENERAL TOLERANCES (unless specified)	UNITS	MM	DATE	2014-03-05
			X.X±0.4	SCALE	1:1	DRAWING	Liu zhi guo
			X.XX±0.25	REV	A	CHECKED BY	Li peng
			X.XXX±0.15			APPROVAL BY	OYSW



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

PRODUCT NAME 3.0 mm right angle header

PART NUMBER H3000S14-XX