


| REV. | ECN NO | LOCATIONS | DESCRIPTION | DATE |
|------|--------|-----------|-------------|------|
|      |        |           |             |      |



- Note:
- Material:
    - Housing: High temperature thermoplastic with g.f,UL94v-0
    - Contact: copper alloy,t=0.15mm
    - Shell: copper alloy,t=0.30mm
  - Specification:
    - Current rating: 1 A Max.
    - Dielectric withstanding voltage: 100 V(ac) for 1 min.
    - Contact resistance: 50 mW Max.
    - Insulation resistance: 100 MW Min.
    - Total mating force: 3.57 Kgf Max.
    - Total unmating force: 1.0 Kgf Min.0.81~2.05 Kgf Min.
    - Temperature range: -30°C~80°C

|                       |          |                    |  |  |        |
|-----------------------|----------|--------------------|--|--|--------|
| PART NO: TCB0007      |          | MATERIAL: SEE NOTE |  | <b>连兴旺电子(深圳)有限公司</b><br><small>LXWCONN ELECTRONICS (SHENZHEN) CO., LTD</small> |        |
| MODEL NO: XX          |          | FINISH: SEE NOTE   |  |  |        |
| UNIT: MM              | SIZE: A4 | COLOR: SEE NOTE    |  | TITLE:   |        |
| TOLERANCE UNSPECIFIED |          | DR: 夏友红            |  | MIRCO USB 5S B TYPE 四脚全插牛角型短针  |        |
| .x                    | 0.25     | CHK:               |  | DWG NO: A067   | REV: B |
| .xx                   | 0.15     | APP:               |  | SCALE: 5:1   |        |
| .xxx                  | 0.10     |                    |  | DATE: 2012.05.02   |        |
| Ang.                  | 2'       |                    |  |  |        |