




由 Autodesk 教育版产品制作

REV NO/??	REVISION NOTE/????	DATE/??	SIGNATURE/??
A/1	RELEASED/??	2013.12.06	GUOWEILONG



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.0A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触电阻: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘电阻: Insulation Resistance:  
1000MEGA ohms MIN

物理性能: Mechanical:








1. 插拔力: Connector Mate and Unmate Force  
Mate force: 3.57kgf(MAX)  
Unmate force: 1.02kgf(MIN)

原材料: Material:

1. 塑胶: Housing:  
Hing Temperature Ternmaplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/不锈钢201

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Talls  
端子四周镀50U"(MIN)锡, 镀金区域镀100-200U"镀金1U"
2. 外壳: Shell:  
外壳四周镀80U"(MIN)锡  
Nickel Plating



连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS(SHENZHEN) CO.,LTD	TOLERANCE UNSPECIFIED ±0.05 ?????	
	UNIT ?? mm	DESIGNED ?? Kelly
PART_NUMBER: TCB0009	SCALE 1:1	CHECKED ??
DRAWING_NUMBER: ????	SHEET ?? 1/1	APPROVED ??

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作