

符合RoHS环保要求

项目 Items	修改内容 Modification	日期 Date	修改人 Draw	批准 Approve
△				

规格说明: Specifications:

电气特性: Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触电阻: Contact Resistance
30 milliohms MAX
- 耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
- 绝缘电阻: Insulation Resistance:
1000MEGA ohms MIN

- 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
- 端子保持力: Terminal Retention
1.0kgf(MIN)

- 塑胶: Housing:
Hing Temperature Ternmaplastics,

- 端子: Contact: Copper Alloy C2680

- 外壳: Shell: Stainless steel 201

电镀: Finish:

- 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails

端子间距 60U"(MIN) - 100U", 镀金 1U"

- 外壳: Shell:
外壳镀层 80U"(MIN) 镍

Nickel Plating

PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	SSRX-
6	SSRX+
7	GND
8	SSTX-
9	SSTX+
Shell	Shield

LXW 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD		DATE		UNIT	MM	DRAWING	DWG NO.	DWG NO.	TCB967
.X±0.15	X±5'	DATE	CHECKED	SCALE	1:1	设计	JUFU	品名	插拔器
XXX±0.02	.XX±1'	APPROVE	角注	VIEW		版本	VER	页数	002

