





PROPRIETARY INFORMATION
COMPANY CONFIDENTIAL





REV.	ECN. NO.	DESCRIPTION	ENG	DATE



3D VIEW



- CONTACT CURRENT RATING: 1A.
- CONTACT RESISTANCE: 100 mΩ MAX.;
- INSULATION RESISTANCE: 100MΩ MIN.;
- DIELECTRIC WITHSTANDING: 500V AC MIN.;
- DURABILITY: 5,000 CYCLES MIN.;
- CONNECTOR MATING FORCES: 30N MAX.;
- CONNECTOR UNMATING FORCES: 3N MIN.;



7	HOUSING	1	HIGHT TEMPERATURE PLASTIC; COLOR BLACK	T=0.20mm
6	TERMINAL 6#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL; GOLD FLASH PLATING ON SOLDER AREA; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
5	TERMINAL 5#	1		T=0.20mm
4	TERMINAL 4#	1	STAINLESS STEEL; NICKEL UNDER PLATING OVERALL; GOLD FLASH PLATING ON SOLDER AREA; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
3	TERMINAL 3#	1		T=0.20mm
2	TERMINAL 2#	1	COPPER ALLOY; NICKEL UNDER PLATING OVERALL; GOLD FLASH PLATING ON SOLDER AREA; GOLD FLASH PLATING ON CONTACT AREA	T=0.20mm
1	TERMINAL 1#	1	COPPER ALLOY; THE BOTTOM OF THE NICKEL; THE WHOLE GOLD PLATING	T=0.20mm
ITEM	NAME	Q'TY	DESCRIPTION	NOTE

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:		ANGLES:	
DIM	TOL	DIM	TOL
X.	±0.50	X.	±2°
X.X	±0.30	X.X	±1°
X.XX	±0.20	X.XX	—
X.XXX	±0.10	X.XXX	—

DWG NO.		PART NAME:	
DESIGN:		ø2.5mm PHONE JACK H=3.2 mm SMT TYPE CONNECTOR	
CHECK:		PART NO.	
APPROVED		PJ25A001-F06J1BR-A	
REV.	UNIT:	SHEET:	
A	mm	1/1	

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD