

电气特性/Electrical Specification

额定参数/Rated	300V 10A
绝缘电阻/Insulation Resistance	5000MΩ/1000V
抗电强度/Dielectric Strength	2000V/1 min

机械特性/Mechanical Specification

使用温度/Temp range	-40° C ~ +105° C
瞬间温度/MAX Soldering	+250° C 5s
扭矩/Torque	0.4Nm
剥线长度/Strip length	6.0-7.0mm
线径/Wire range	24-12AWG

部件材质/Part&Material

塑件/Housing	PA66 UL94 V-0
螺丝/Screws	钢 镀锌/Steel Zn plating
方块/Cage	黄铜 镀镍/Brass Ni plating
焊针/Pin header	黄铜 镀锡/Brass Tin plating

间距公差/Spacing tolerance(mm)

X.	X.X	X.X.X	0.1/10
±0.5	±0.30	±0.1	∠ ±2°

未注公差/General tolerances(mm)

0---30	31---50	51---80	81---120	>121
±0.30	±0.50	±0.70	±1.05	±1.20




连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

STATUS APPD CHKD DRFT DATE CUSTOM PROJECT UNITS

ZH



MM

PART NAME:

PART NO:LXW128-5.0-NP

DRAWING NO:

TYPE: CUSTOMER DRAWINGS

REV SIZE SHEET

A A4 1/1