



REV.	DESCRIPTION	APPD	DATE
△/A	外壳弹片改直	杨凯	0925'10
△/A	尺寸0.70改为0.55	杨凯	0925'10
△/A	尺寸3.50改为2.30	刘静	1115'11
△/A	主体底部增加孔位	杨凯	0826'12
△/A	增加CD PIN 高低管控	刘静	20121219



NOTES:
 1.MATERIAL:
 HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V_0,COLOR:BLACK.
 CONTACT: COPPER ALLOYS.
 COVER: COPPER ALLOYS OR STEEL.
 2.PLATING:
 UNDERPLATE: NICKEL.
 CONTACT AREA: GOLD OVER NICKEL.
 SOLDER AREA: TIN OVER NICKEL.
 3.MULTIMEDIA CARD COMPATIBLF



PIN NO.	NAME	YTYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DATO	I/O/PP	DATE LINE(BITO)
8	DAT1	I/O/PP	DATE LINE(DIT1)
9	CD	CD	CD

RECOMMENDED P.C.B HOLE LAYOUT
 COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

PART NO: LXW-TF001		MATERIAL:		连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS(SHENZHEN) CO.,LTD
LOT NO:		FINSH:		
UNIT: MM	SIZE: A4	COLOR:		TITLE: T-FLASH 外焊 PUSH 有压片
TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15		GENERAL ANGLE: X.X=±3.0° X.XX=±2.0°		DR: PENTIU 0826'09
APP:		DWG NO: FP-090012	SCALE: 1:1	REV: E
		SHEET: 1 OF 3		