

RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
△	原始图档		JACK		150606

Material

Insulator:Nylon 9T(UL94V-0)

TERMINAL:phosphor Bronze

TERMINAL Plated:Gold over Nickel
or Tin

Specification

Current rating:7A

instant CURRENT:10A




Contact Resistance:30MΩ

Insulation Resistance:100MΩ

Dielectric Voltage:500V


Operdting Temperature:-40°~105°

No. of Pins	Dimension		
	DIM. A	DIM. B	DIM. C
02	7.00	2.50	7.0/8.0
03	9.50	5.00	7.0/8.0
04	12.00	7.50	7.0/8.0
05	14.50	10.00	7.0/8.0
06	17.00	12.50	7.0/8.0
07	19.50	15.00	7.0/8.0
08	22.00	17.50	7.0/8.0
09	24.50	20.00	7.0/8.0
10	27.00	22.50	7.0/8.0
11	29.50	25.00	7.0/8.0
12	32.00	27.50	7.0/8.0
13	34.50	30.00	7.0/8.0
14	37.00	32.50	7.0/8.0
15	39.50	35.00	7.0/8.0
16	42.00	37.50	7.0/8.0



Recommended P.C.B Layout

Layout Tolerance=+/-0.05mm



QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)				SCALE: 1:1	NUMBER:	东莞市文章济美电子有限公司			
▽_A		MM		INCH	MATERIAL:	HRC:					
	. X	±0.25	. X	②	DRAWN BY DATE		TITLE: Battery 2.5PH 180度DIP 7.0/8.0H 公座				
	. XX	±0.15	. XX	③							
	. XXX	±0.05	. XXX	④	CHECKED BY DATE		 THIRD ANGLE PROJECTION REVISE ON CAD ONLY				
	ANGULAR ±1°										
▽_C	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				APPROVED BY DATE		PART NO. JME25Mxx-H080001A-B		DWG NO.	SHEET NO. 1/1	
						A4					