








P.C.B Layout

NOTES:

1. Material:
Insulation: PA9T, UL94V-0(White)
Pin:Phosphor bronze/Tin-Plated
Tab:Phosphor bronze/Tin-Plated
2. Current Rating: 1A AC,DC
3. Voltage Rating: 125V AC,DC
4. Temperature Rang: -25°C~+85°C
5. Stroage Temperature Rang: <30°C 60%RH
6. Contact Resistance: 20mΩ Max
7. Insulation Resistance: 100MΩ Min
8. Withstanding Voltage: 500V AC/minute

Poles	PART NO.	Dimension mm		
		A	B	C
2	W-NH10N02P-B000	1.00	3.70	2.50
3	W-NH10N03P-B000	2.00	4.70	3.50
4	W-NH10N04P-B000	3.00	5.70	4.50
5	W-NH10N05P-B000	4.00	6.70	5.50
6	W-NH10N06P-B000	5.00	7.70	6.50
7	W-NH10N07P-B000	6.00	8.70	7.50
8	W-NH10N08P-B000	7.00	9.70	8.50
9	W-NH10N09P-B000	8.00	10.70	9.50
10	W-NH10N10P-B000	9.00	11.70	10.50
11	W-NH10N11P-B000	10.00	12.70	11.50
12	W-NH10N12P-B000	11.00	13.70	12.50
13	W-NH10N13P-B000	12.00	14.70	13.50
14	W-NH10N14P-B000	13.00	15.70	14.50
15	W-NH10N15P-B000	14.00	16.70	15.50

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: NH1.0SMT-XP 带扣 立贴						
DRAWN: LYF	DATE: 2025-05-07	PART. NO.		W-NH10NXXP-B000				
		UNIT	mm	SCALE	free			
		FILE NO.		Ckmtw-NH1.0-B004		REV.	A	XR00