

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20m Ω Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000M Ω Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Dimension antitheses list				
ITEM	PA	PC	C	L
Standard	6.00	3.00	5.00	14.00
Alternate				

Ordering Information

PZ 254 - * - N - Z - * - ** - DP

No. of Rows
1=Single Row
2=Double Row
3=Triple Row

No. of Pins
02-40Pin

Type
2=直插
3=贴片
4=贴片

Length
(产品长度)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Dual Plastic
(双塑)

			GENERAL TOLERANCE		制图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核				
			X.X	± 0.30	批准	产品名称	2.54 三排 双塑 直排针	版本	A
			X.XX	± 0.20	APPROVAL	TITLE		REV.	
			X.XXX	± 0.10	比例	产品料号	PZ254-3-N-Z-C5.0-XX-DP (L14.0)	单位	mm
			Angle	$\pm 3.0^\circ$	SCALE	PART NO.		UNITS	
序号	变更内容	日期	投影		投影	材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection		Projection	MATERIAL		SHEET	