





Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS  
 Rated Current:1.5AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 5 seconds)



Dimension antitheses list				
ITEM	PA	PC	C	L
Standard	3.90	2.80	4.20	10.90
Alternate				

**Ordering Information**

PZ 200 - \* - N - \* - \* - \*\* - DP

No. of Rows 1=Single Row 2=Dual Row	No. of Pins 02-40Pin	Type Z=直针 W=弯针 S=立脚 WS=接插	Length (塑高)	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Double Plastic (双塑)
-------------------------------------------	-------------------------	---------------------------------------	----------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------------

			GENEAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	2.00双排 双塑 直排针	版本 REV.	A
			X. X ±0.30	批准 APPROVAL	产品料号 PART NO.	PZ200-2-N-Z-C4.2-XX-DP(L10.9)	单位 UNITS	mm
1	初版发行		X. XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X. XXX ±0.10	投影 Projection				
			Angle ±3.0°					