



ENGLISH

SPECIFICATION SHEET

RS Stock No 365543

SOFT TINNED COPPER WIRE BRAID 2534P

CONSTRUCTION : 24x10x0.20MM

RESISTANCE : 2.3 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.

YIELD : 80.4KGS/1000M

TENSILE : N/A

WIRE : MANUFACTURED TO BSEN 13602: 2002

RoHS : COMPLIANT