



Item Code	Rated Voltage	Frequency (Hz)	Rated Current (A)	Input Power (W)	Max. Air Flow		Noise dB(A)	Capacitor (uF)
					CFM	m3/min		
AA1V250-80T-FMC-B1-2C	115V	50/60	1.14/1.60	129/180	1065/1170	30.2/33.1	68/70	16 F/250VAC
AA2V250-80T-FMC-B1-2C	230V	50/60	0.57/0.79	130/179	1058/1162	30.0/32.9	68/70	4 F/450VAC

Item	Description	Revision	Date	Revised	Applied Item

Unit	mm	Scale	Date	100/03/07	Drawn	Checked	DWG No.	0
------	----	-------	------	-----------	-------	---------	---------	---



Model No.

AA250-80T-無框