


Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)





SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)


Dimension antitheses list			
ITEM	PA	PB	W
Standard	4.00	1.50	5.50
Alternate			



P = With Post

默认 = W/O Post

Ordering Information



			GENE RL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK	产品名称 TITLE	1.27双排 双塑 排针 贴片	版 本 REV.	A
			X.X ±0.30	批 准 APPROVAL	产品料号 PART NO.	PZ127-2-N-S-C5.0-XX-DP(L9.5)	单 位 UNITS	mm
1	初版发行		X.XX ±0.20	比 例 SCALE	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投 影 Projection				
			Angle ±3.0°					