




D		E		F		
版次	变更摘要	日期	序号	品名	材质	
0	新产品发行	2016/9/25	①	1.25-J型卧式WTB胶芯	PA6T UL94V-0 米黄色	
			②	1.25-J型卧式WTB端子	铜合金/表面镀金 表面镀锡	
			③	1.25-J型卧式WTB焊片	铜合金/表面镀锡	

7. 产品料号:
5001 - MX 0125 A - ** R 1 -00
JM CONNECTOR SERIES
PITCH:1.25
A: 卧贴
ALTERNATE
PACKING:R: 卷
PIN



SECTION A-A



2~3 Pin结构外形(锁扣窗口)




CKT	DIM A	DIM B	DIM C	DIM D
2	1.25	3.87	7.60	0.00
3	2.50	5.12	8.85	0.00
4	3.75	6.37	10.10	2.50
5	5.00	7.62	11.35	3.75
6	6.25	8.87	12.60	5.00
7	7.50	10.12	13.85	6.25
8	8.75	11.37	15.10	7.50
9	10.00	12.62	16.35	8.75
10	11.25	13.87	17.60	10.00
11	12.50	15.12	18.85	11.25
12	13.75	16.37	20.10	12.50
13	15.00	17.62	21.35	13.75
14	16.25	18.87	22.60	15.00
15	17.50	20.12	23.85	16.25
16	18.75	21.37	25.10	17.50
17	20.00	22.62	26.35	18.75
18	21.25	23.87	27.60	20.00
19	22.50	25.12	28.85	21.25
20	23.75	26.37	30.10	22.50

深圳市文章济美科技有限公司

品名 (TITLE)	1.25 Pitch J型卧式WTB		制图 (DR)	Anlan	
料号 (DWG.NO)	5001-MX0125A-**R1-00-B		校对 (CHKD)	王涛	
比例 (SCALE)	1:1	单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
				SIZE	A4
				REV	A



一般公差 (TOLERANCE)
X ±.50 XX ±.10
X ±.20 XXX ±.05
ANGLES ±1°



技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40° C~85° C.
3. 额定电压: 125V, AC/DC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ.
6. 额定电流:
适用电线型号: a. AWG#28:2.5A(per pin)
b. AWG#30:1.0A(per pin)
c. AWG#32:0.8A(per pin)

