



Recommended PCB board layout
Size tolerance: ± 0.05

NOTES:

- 1) MATERIAL:
 - 1-1 HOUSING:THERMOPLASTIC LCP UL 94V-0,COLOR:WIHITE
 - 1-2 CONTACT:SUS304 T=0.10mm
- 2) FINISH:
 - CONTACT:G/G PLATING ON SOLDER TAILS
 - 50u"MIN.NI UNDERPLATING
- 3) PRODUST SPECIFICATIONS;
 - 3-1 VOLTAGE RATING:30V
 - 3-2 CURRENT RATING:0.5A
 - 3-3 CONTACT RESISTANCE;30 milliOHM(Initial) Max.
 - 3-4 INSULATION RESISTANCE:100 MEGOHM Min.
 - 3-5 OPERATION TEMPERATURE:-25° TO +85°
 - 3-6 CONTACT NORMAL FORCE 40~80gf



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 电池弹片 2PIN 3.2H 正向柱
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HVCW-TXT692532B
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HVC-2601231150
			SHEET NO. 1 OF 1