


客户确认:	
日期:	



注意事项:

- 1: 线材H1 H2 H3端剥皮2.0mm压接2001T端子,
- 2: 端子拉力1.5KG
- 3: 100%导通
- 4: 按照图纸接点穿胶壳

接点表

H1	H2	H3
1	8空	
2	7	10空
3	6	9空
4	5	8空
5	4	7
6		6
7		5
8	3	
9		4
10		3
11		2
12		1
13	2	
14	1	

5	胶壳:	2001H-8P (PH2.0间距胶壳) 白	2	PCS
4	胶壳:	2001H-10P (PH2.0间距胶壳) 白	12	PCS
3	胶壳:	2001H-14P (PH2.0间距胶壳) 白	2	PCS
2	端子:	2001T (PH2.0端子)	12	PCS
1	线材:	UL1007#26 黑 X14	215	mm
序号	名称	规格	用量	单位

APPROVED:	DATE:	XPB 深圳市鑫鹏博电子科技有限公司 SHENZHEN XINPENGBO ELECTRONICS CO. LTD					
CHECKED:	DATE:	TITLE: 3H-2001H-14P+2001H-10P+2001H-8P+UL1007-26AWG L=180MM					
DRAWN:	DATE:	CLIENT P/N:					
LQW	2025-12-06	UNIT:	mm	SCALF:	free	⊕	◁
		FILE NO.	XPB11780030		REV.	A	