

版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2021/06/03	①	VH3. 96卧式WTB胶芯	LCP UL94V-0本色
			②	VH3. 96卧式WTB端子	铜合金/表面镀锡
			③	VH3. 96卧式WTB焊片	铜合金/表面镀锡

技术指标:





1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 250V, AC DC.
4. 额定电流: 7.0 A, AC DC.
4. 接触电阻: ≤30mΩ Min,
5. 绝缘电阻: ≥1000MΩ.
6. 耐压值: 1500V AC/minute.
7. 产品料号: 5001 - VH 0396 A - ** R 1-00
- JM CONNECTOR SERIES
- PITCH: 3.96
- A: 卧贴
- ALTERNATE
- PACKING: T(管); R(卷)
- PIN

CKT	A	B	C	D	E
2	3.96	8.68	10.61	11.88	3.88
3	7.92	12.64	14.57	15.84	7.84
4	11.88	16.60	18.53	19.80	
5	15.84	20.56	22.49	23.76	
6	19.80	24.52	26.45	27.72	
7	23.76	28.48	30.41	31.68	
8	27.72	32.44	34.37	35.64	
9	31.68	36.40	38.33	39.60	
10	35.64	40.36	42.29	43.56	10.00
11	39.60	44.32	46.25	47.52	
12	43.56	48.28	50.21	51.48	
13	47.52	52.24	54.17	55.44	
14	51.48	56.20	58.13	59.40	
15	55.44	60.16	62.09	63.36	
16	59.40	64.12	66.05	67.32	




深圳市文章济美科技有限公司

品名 (TITLE)	制图 (DR)
VH3. 96卧式WTB业务图	校对 (CHKD)
料号 (DWG.NO)	审核 (APPD)
VH0396A-R1-00-B	
比例 (SCALE)	单位 (UNITS)
1:1	mm
张数 (SHEET)	SIZE
1 OF 1	A4
REV	A

一般公差 (TOLERANCE)
X. ±0.50 .XX ±1.0
X. ±0.20 .XXX ±0.05
ANGLES ±1°



适用线路板 (厚度: 0.8mm~1.6mm)



Assembly Layout